

# BLUESIL RTV 3720 A&B. RTV 3720 SC A&B

<b>Description</b>	<p>The <b>BLUESIL RTV 3720 A&amp;B</b> is a two component silicone elastomer which cures at room temperature by a polyaddition reaction (1:1 ratio).</p> <p>The material can be applied onto horizontal as well as vertical surfaces thanks to its slight thixotropic behaviour, by means of casting or solventless spraying in both cases a silicone film is obtained.</p> <p>The product is available in two versions:</p> <ul style="list-style-type: none"> <li>• <b>RTV 3720 A&amp;B</b>: Fast cure, for spray application</li> <li>• <b>RTV 3720 SC A&amp;B</b>: Slow cure, for casting application</li> </ul>
<b>Examples of applications</b>	<p>The <b>BLUESIL RTV 3720 A&amp;B</b> is specifically developed to produce a silicone bag on molds used for the processing of composites applying the "vacuum resin infusion" technology. The material is not limited to this application.</p>
<b>Key benefits</b>	<ul style="list-style-type: none"> <li>• Excellent mechanical properties.</li> <li>• Low viscosity (easy sprayable) with thixotropic behavior.</li> <li>• Choice between very fast cure and long open time cure (both room temperature)</li> <li>• High chemical resistance.</li> <li>• No release of toxic substances during and after curing.</li> </ul>

**Typical properties** 1. Characteristics of the non cured product

Properties	BLUESIL RTV 3720 and BLUESIL RTV 3720 SC	
	PART A	PART B
Appearance	Viscous liquid	
Colour	Translucent	Light blue
Viscosity (mPa.s, approx.)	30 000	
Specific gravity (g/cm <sup>3</sup> , approx)	1.08	1.10

2. Polymerization

The following ratio applies to any version of **BLUESIL RTV 3720 A&B**:

**PART A**: 100 parts

**PART B**: 100 parts

Properties	BLUESIL RTV 3720 A&B	BLUESIL RTV 3720 SC A&B
Colour	Light blue	Light blue
Pot life (at 23°C, 50% Relative Humidity, minutes)	3	25
Demolding time (at 23°C, 50% Relative Humidity, minutes)	15	90

# BLUESIL RTV 3720 A&B. RTV 3720 SC A&B


**Remark:** Higher temperatures reduce pot life, lower temperatures increase it. If curing is accelerated by heat the properties of **RTV 3720 A&B** are not modified, however dimensional changes might occur during post curing of the elastomer which must be taken into account.

## Principle of crosslinking:

**BLUESIL RTV 3720 A&B** cures by polyaddition reaction.

This kind of curing is based on reaction of silicone reactive groups  $\equiv\text{SiH}$  with silicone unsaturated polymers such as  $\equiv\text{Si-CH=CH}_2$ .

This reaction may be summarized as follows :



This reaction can be accelerated by heat.

## 3. Cross linked product

Measured after curing 24 hours at 23°C

Properties	BLUESIL RTV 3720 A&B BLUESIL RTV 3720 SC A&B
Hardness Shore A ( <i>Shore A, on 6 mm thick specimen, approx.</i> )	20
Tensile Strength at break ( <i>MPa, approx.</i> )	4
Elongation at break ( <i>%, approx.</i> )	500
Tear strength ( <i>kN/m, approx.</i> )	15
Linear shrinkage (%)	< 0.2

Please note: The typical properties are not intended for use in preparing specifications. Please contact our local Sales Department for assistance in writing specifications.

## Instruction of use

### 1. Mixing of the two components

The material can be processed differently according to the version:

#### **BLUESIL RTV 3720 A&B:**

Add 100 parts of **BLUESIL RTV 3720 A** to 100 parts of **BLUESIL RTV 3720 B**.

**BLUESIL RTV 3720 A&B** should only be used by means of a spray or injection equipment with a meter/static mixer, as the pot life is too short to hand-mix and efficiently degas the material.

#### **BLUESIL RTV 3720 SC A&B:**

Add 100 parts of **BLUESIL RTV 3720 SC A** to 100 parts of **BLUESIL RTV 3720 SC B**.

The two components may be intimately mixed either by hand or using a low-speed electric or pneumatic mixer to minimize the introduction of air into the mixture.

### 2. Degassing

After mixing parts A&B of **BLUESIL RTV 3720 SC** it is recommended to degas the product to eliminate the entrapped air introduced in the mixture. The standard (quick-cure) version is

# BLUESIL RTV 3720 A&B. RTV 3720 SC A&B

usually processed using an automatic dosing machine with a static mixer, and by degassing previously each of the two parts, air is not introduced during the mixing.

**BLUESIL RTV 3720 SC** can be degassed under a 30 to 50 mbar vacuum. When the vacuum is applied the product expands 3-4 times its initial volume and bubbles form on the surface. Once bubbles disappear, the mixture collapses back to its initial volume. To complete degassing simply wait few minutes before releasing the vacuum. then the product will then be ready to use.

**Remark:** pull and release the vacuum several times improves the degassing. For easier degassing only fill a recipient only to 1/3 of its height.

Pour the degassed mixed material slowly in a steady stream from one edge of the mold box so that the material flows evenly over the model minimizing the entrapment of air bubbles under the flowing silicone.

### **3. Cross linking**

At room temperature (23°C) **BLUESIL RTV 3720 A&B** cures in the given demolding time regardless of the mold thickness. For best results the mold should be allowed to fully cure for 24 hours before using it for production.

Room temperature curing assures the lowest possible shrinkage, if accelerated cure of the **SC** version is desired, mild heat should be preferred. To minimize shrinkage, the elastomer can be cured at temperature of 60°C for 1 hour, higher temperatures might cause higher shrinkage.

Conversely at lower temperature polymerization is much slower: at 10°C the time necessary to complete cross-linking will be almost double the time at 23°C.

Be aware that contact with certain materials can inhibit the curing of this RTV:

- Natural rubbers vulcanized with sulphur
- Polycondensation RTV catalysed with metal salts
- PVC stabilizing agents
- Amine cured epoxies
- Sulphur containing clays.

In case of doubts it is recommendable to run a quick test with a small quantity of material in order to assess compatibility. Take note that cross contamination due to not well cleaned tools or devices is frequently the main causes of inhibition. The best way is to use only dedicated gear when processing polyaddition RTVs.

### **4. Available tools**

Following materials can provide an efficient way to customize the application of **BLUESIL RTV 3720 A&B** matching the own process needs:

- Retarder Additive to increase working time (for both versions)
- Accelerator Additive to shorten working time (for SC version)
- Thixotropic Additive to adjust the product rheology (for SC version)
- Silicone Adhesive to repair eventual damages
- Silicone Paste to protect sharp mold edges

Please refer to the corresponding product datasheet for detailed information about the tools properties and their correct application.

# BLUESIL RTV 3720 A&B. RTV 3720 SC A&B

<b>Regulation</b>	Please consult your local ELKEM SILICONES sales office.
<b>Limitations</b>	Please consult your local ELKEM SILICONES sales office.
<b>Packaging</b>	<ul style="list-style-type: none"> <li>• BLUESIL RTV 3720 A is available in                             <ul style="list-style-type: none"> <li>○ Drum of 25 KG (55.13 LB)</li> </ul> </li> <li>• BLUESIL RTV 3720 B is available in                             <ul style="list-style-type: none"> <li>○ Drum of 25 KG (55.13 LB)</li> </ul> </li> <li>• BLUESIL RTV 3720 SC A is available in                             <ul style="list-style-type: none"> <li>○ Drum of 200 KG (441 LB)</li> <li>○ Pail of 25 KG (55.13 LB)</li> <li>○ Pail of 10 KG (22.05 LB)</li> </ul> </li> <li>• BLUESIL RTV 3720 SC B is available in                             <ul style="list-style-type: none"> <li>○ Drum of 200 KG (441 LB)</li> <li>○ Pail of 25 KG (55.13 LB)</li> <li>○ Pail of 10 KG (22.05 LB)</li> </ul> </li> </ul>
<b>Storage and shelf life</b>	<p>When stored in its original packaging:</p> <p>BLUESIL RTV 3720 A may be stored at temperatures between -5°C / 23°F and 30°C / 86°F for up to 12 months from its date of manufacturing.</p> <p>BLUESIL RTV 3720 B may be stored at temperatures between -5°C / 23°F and 30°C / 86°F for up to 12 months from its date of manufacturing.</p> <p>BLUESIL RTV 3720 SC A may be stored at temperatures between -5°C / 23°F and 30°C / 86°F for up to 12 months from its date of manufacturing.</p> <p>BLUESIL RTV 3720 SC B may be stored at temperatures between -5°C / 23°F and 30°C / 86°F for up to 12 months from its date of manufacturing.</p> <p>Comply with the storage instructions and expiration date marked on the packaging. Beyond this date, Elkem Silicones no longer guarantees that the product meets the sales specifications.</p>
<b>Safety</b>	<p>Please consult the Safety Data Sheet of:                      BLUESIL RTV 3720 A, BLUESIL RTV 3720 B, BLUESIL RTV 3720 SC A and BLUESIL RTV 3720 SC B</p>

Visit our website [www.elkem.com/silicones/](http://www.elkem.com/silicones/)

#### Warning to the users

The information contained in this document is given in good faith based on our current knowledge. It is only an indication and is in no way binding, particularly as regards infringement of or prejudice to third party rights through the use of our products. ELKEM SILICONES guarantees that its products comply with its sales specifications. This information must on no account be used as a substitute for necessary prior tests which alone can ensure that a product is suitable for given use. Determination of the suitability of product for the uses and applications contemplated by users and others shall be the sole responsibility of users. Users are responsible for ensuring compliance with local legislation and for obtaining the necessary certifications and authorisations. Users are requested to check that they are in possession of the latest version of this document and ELKEM SILICONES is at their disposal to supply any additional information.