

BLUESILTM RTV 3428 A & B

Description

The **BLUESIL RTV 3428 A&B** is a two component silicone elastomer which cures at room temperature by a polyaddition reaction.

This reaction can be accelerated by heat.

Examples of applications

- Production of flexible moulds with excellent details reproduction, mechanical resistance and duration.
- Production of thermal expansion formers for composite materials (the aeronautic industry, boat-building, etc.).
- Production of moulds intended for moulding objects in chocolate, sugar, marzipan and for producing decorative sugar, pieces of bakery, biscuits and confectionery products.

Advantages

- Easy processing and curing.
- Outstanding tensile and tear strength.
- Low linear shrinkage (when crosslinked at room temperature).
- PART B: different colours available (see characteristics).
- Once cured according to the conditions given in this technical data sheet, the chemical composition of **BLUESIL RTV 3428 A&B** conforms with the positive lists of products approved by the regulations in force in the following countries:
 - **FRANCE:** Journal Officiel, Brochure 1227
 - **GERMANY:** BGA, chapter XV-A
 - **UNITED STATES:** FDA Regulations, CFR-2 1

For regulated applications, please contact Bluestar to ensure compliance and obtain the relevant statement.

Characteristics

1. Characteristics of the non cured product

Properties	BLUESIL RTV 3428 A	BLUESIL RTV 3428 B
Appearance	Viscous liquid	
Color	Colorless	Pink, White, Colorless
Specific gravity (At 23°C, g/cm ³ , approx.)	1.1	1.1
Viscosity (At 23°C, mPa.s, approx.)	25 000	8 000

BLUESIL™ RTV 3428 A & B**Characteristics**
(cont')**2. Polymerization****BLUESIL RTV 3428 A**.....100 parts**BLUESIL RTV 3428 B**10 parts

<i>Properties</i>	BLUESIL RTV 3428 A&B
Pot life (at 23°C, hours)	1
Demoulding time (at 23 °C, hours)	16

Note: heat-accelerated crosslinking does not affect the properties of **BLUESIL RTV 3428 A&B**. However, dimensional changes do occur that should be kept into account.

3. Characteristics of the cross linked product

Measured after curing 24 hours at 23°C

<i>Properties</i>	BLUESIL RTV 3428 A&B
Hardness (Shore A, on a 6 mm thick specimen, approx.)	28
Tensile strength at break (MPa, approx.)	7.5
Elongation at break (%, approx.)	600
Tear strength (KN/m, approx.)	20
Linear shrinkage (%, 7 days after curing at 23°C)	0.1

Processing**Remix each of the two components (part A and B) every time before using.****1. Mixing of the two components**

Add 100 parts of **BLUESIL RTV 3428 A** to 10 parts of **BLUESIL RTV 3428 B**. The two components may be intimately mixed either by hand or using a low-speed electric or pneumatic mixer to minimize the introduction of air into the mixture.

The viscosity of **BLUESIL RTV 3428 A&B** can be reduced by using BLUESIL FLD 47V50, added up to 10% with respect to **BLUESIL RTV 3428 A**. This will improve flowing of the mixed product without causing significant changes of the mechanical properties of the elastomer.

Under no circumstances should this process can be applied for food moulding. In that case, the product must be used in its original formulation without any dilution, whatever it is.

BLUESIL™ RTV 3428 A & B**Processing (cont')****2. Degassing**

After mixing base and catalyst, it is recommended to eliminate entrapped air.

If the mixing is done with the help of a machine and a static mixer, both parts are degassed before mixing.

BLUESIL RTV 3428 A&B is degassed under a vacuum of 30 to 50 mbar. The degassing of the mixed product or of the two separated parts occurs under a vacuum of 30 to 50 mbar. Under vacuum, the product expands 3 to 4 times its initial volume and forms bubbles on its surface. These bubbles will disappear gradually and the mixture will sink back down to its initial volume within 5 minutes. Release the vacuum and repeat the operation a few minutes later.

***Remark:** release the vacuum several times improves the degassing. For easier degassing only fill a recipient to 1/3 of its height.*

The product can be casted by gravity or under pressure.

3. Cross linking

The best curing conditions are at 23°C. When using the products at higher temperatures, the pot life is shorter and the setting rate faster. As opposed to this, lower temperatures increase the pot life and decrease the setting rate.

Room temperature curing assures the lowest possible shrinkage, if accelerated cure is desired, mild heat should be preferred. To minimize shrinkage the elastomer should be cured at maximum temperature of 60°C. Higher temperatures might cause higher shrinkage.

At 23°C, the cured silicone can be demoulded after the time indicated as "demolding time" (see § 2. *Polymerization*). In order to achieve the best possible performance levels from the pads, it is preferable to wait for 24 hours before using them.

Be aware that contact with certain materials can inhibit the curing of this RTV:

- Natural rubbers vulcanized with sulphur
- Polycondensation RTV catalysed with metal salts
- PVC stabilizing agents
- Amine cured epoxies
- Sulphur containing clays

In case of doubts, it is recommended to test the substrate by applying a small quantity of the mixed silicone on a restricted area. Take note that cross contaminations due to improperly cleaned tools or devices is the most frequent cause of inhibition.

Use of BLUESIL RTV 3428 A + 3428 B ALL COLORS for the production of moulds for direct contact with food preparations

If cured according to the instructions described in the paragraph *Characteristics* of this datasheet, the chemical composition of **BLUESIL RTV 3428 A&B ALL COLORS** conforms with the positive lists of products approved by the regulations in force in the following countries: **FRANCE: Journal Officiel, Brochure 1227; GERMANY: BGA, chapter XV-A; UNITED STATES: FDA Regulations, CFR-2 1.**

In all cases, the mould manufacturers must check that the moulds, in their future conditions of use, satisfy the EEC directive relative to migration tests: **European Directive 93/8/EEC.**

BLUESIL™ RTV 3428 A & B**Use of BLUESIL RTV 3428 A + 3428 B ALL COLORS for the production of moulds for direct contact with food preparations (cont')**

Purely for information purposes, migration tests have been carried out on prototype moulds in accordance with this directive. The results obtained showed that:

1. In the special case of moulding of fat based products such as chocolate, the contact time between the mould and the melted foodstuff must be minimised: e.g. the duration of contact between the mould and the melted fatty product should not exceed 2 hours and the mould temperature should not exceed 40 °C.
2. In the case of other foodstuff, the moulds may be used without any particular precautions in terms of duration of contact and temperature, whilst remaining within the temperature range compatible with the heat stability of silicone elastomers.

*Note: In order to comply with the above mentioned directives, **BLUESIL RTV 3428 A + 3428 B ALL COLORS** must be mixed in the recommended ratio (A:B 10:1 w/w).*

In food contact application context, under no circumstances should the product be diluted with silicone oil.

Packaging

BLUESIL RTV 3428 A is available in 200 kg metal drums, 20 kg, or 1 kg plastic pails.

BLUESIL RTV 3428 B is available in 20 kg, 2 kg, or 100 g plastic pails.

Storage and shelf life

When stored in their original packaging at a temperature of between –5°C and + 30°C, **BLUESIL RTV 3428 A&B** may be stored for up to 20 months from their date of manufacture.

Comply with the storage instructions and expiry date marked on the packaging.

Beyond this date, Bluestar Silicones no longer guarantees that the products meet the sales specifications.

Safety

Please consult the Safety Data Sheets of **BLUESIL RTV 3428 A&B**.

Visit our website www.bluestarsilicones.com

EUROPE

Bluestar Silicones France
21 Avenue Georges Pompidou
F69486 Lyon Cedex 03
FRANCE
Tel. (33) 4 72 13 19 00
Fax (33) 4 72 13 19 88

NORTH AMERICA

Bluestar Silicones USA
2 Tower Center Boulevard
Suite 1601
East Brunswick, NJ 08816-1100
United States
Tel. (1) 732 227-2060
Fax. (1) 732 249-7000

LATIN AMERICA

Bluestar Silicones Brazil Ltda.
Av. Maria Coelho Aguiar, 215
Bloco G – 1º andar
05804-902-Sao Paulo – SP-
Brazil
Tel. (55) 11 37477887

ASIA PACIFIC

Bluestar Silicones Hong Kong
Trading Co. Ltd
29th Floor, 88 Hing Fat Street
Causeway Bay
Hong Kong
Tel. (852) 3106 8200
Fax (852) 2979 0241

Warning to the users

The information contained in this document is given in good faith based on our current knowledge. It is only an indication and is in no way binding, particularly as regards infringement of or prejudice to third party rights through the use of our products. BLUESTAR SILICONES guarantees that its products comply with its sales specifications. This information must on no account be used as a substitute for necessary prior tests which alone can ensure that a product is suitable for given use. Users are responsible for ensuring compliance with local legislation and for obtaining the necessary certifications and authorisations. Users are requested to check that they are in possession of the latest version of this document and BLUESTAR SILICONES is at their disposal to supply any additional information.